

Series 804 Push/Pull Mighty Mouse
USB Tactical Patch Cable
808-007 Interface Adapter

These cordsets feature ruggedized series 804 Mighty Mouse Push/Pull connectors in a size #6 shell with insert arrangements for 6 pins for both plug and receptacle. Polyurethane cable jacket is suitable for general purpose applications. Mighty Mouse connector is overmolded with polyamide for strain relief and water ingress protection. All pin connectors have first to mate, last to break (FMLB) contact in position 2.

Note: Cable Type D shown for reference only. See Table I and II for Ordering information on polyurethane or Nomex® jacketed cable types.



Wiring Diagram




Dimensions in Inches (millimeters) are subject to change without notice.

© 2014 Glenair, Inc. Series 80 Mighty Mouse U.S. CAGE Code 06324 Printed in U.S.A.


Downloaded from Arrow.com.

Table I: How To Order Cables with Polyurethane Cable Jacket


Basic P/N	Cable Type	Length
808-007	**-A** = Single Ended **-AA** = Double Ended	In inches **12** = 12 in.
Sample Part Number		
808-007	**-A**	**12**




Basic P/N	Cable Type	Length
808-007	**-B** = Single Ended	In inches **12** = 12 in.
Sample Part Number		
808-007	**-B**	**12**




Basic P/N	Cable Type	Length
808-007	**-C** = Single Ended **-CC** = Double Ended	In inches **12** = 12 in.
Sample Part Number		
808-007	**-C**	**12**



Basic P/N	Cable Type	Length
808-007	**-D** = Single Ended	In inches **12** = 12 in.
Sample Part Number		
808-007	**-D**	**12**



Basic Part Number	Cable Type	Length
808-007	**-E** = Single Ended **-EE** = Double Ended	In inches **12** = 12 in.
Sample Part Number		
808-007	**-E**	**12**




Dimensions in Inches (millimeters) are subject to change without notice.

Downloaded from Arrow.com.


Series 804 Push/Pull Mighty Mouse
USB Tactical Patch Cable with Nomex® Jacket
808-007 Interface Adapter

Table 2: How To Order Cables with Nomex Jacket


Basic P/N	Cable Type	Length
808-007	**-G** = Single Ended **-GG** = Double Ended	In inches **12** = 12 in.
Sample Part Number		
808-007	**-G**	**12**




Basic P/N	Cable Type	Length
808-007	**-H** = Single Ended	In inches **12** = 12 in.
Sample Part Number		
808-007	**-H**	**12**




Basic P/N	Cable Type	Length
808-007	**-J** = Single Ended **-JJ** = Double Ended	In inches **12** = 12 in.
Sample Part Number		
808-007	**-J**	**12**



Basic P/N	Cable Type	Length
808-007	**-K** = Single Ended	In inches **12** = 12 in.
Sample Part Number		
808-007	**-K**	**12**



Basic P/N	Cable Type	Length
808-007	**-L** = Single Ended **-LL** = Double Ended	In inches **12** = 12 in.
Sample Part Number		
808-007	**-LL**	**12**



Dimensions in Inches (millimeters) are subject to change without notice.

© 2014 Glenair, Inc.

Downloaded from Arrow.com.