

**Part Number :** 1205010120
**Product Description :** Micro-Change (M12) Double-Ended Cordset, 5 Poles, L-Coded, Female (Straight) to Male (90°), 14 AWG, Gray TPU WSOR Cable, 5.0m (16.40') Length
**Series Number :** 120501
**Status :** Active
**Product Category :** Industrial Cable Assemblies
**Engineering Part Number :** LLP5032B63M050

## Documents and Resources

### Drawings

1205010120_sd.pdf

1205010169-K00.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Relevant |
| EU ELV | Compliant with Exemption 3 per 2000/53/EC |
| Low-Halogen Status | Not Relevant |
| REACH SVHC | Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:740e4330-e996-46f4-ad7e-2f98c76fb902 |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Industrial Cable Assemblies |
| Series | 120501 |
| Description | Micro-Change (M12) Double-Ended Cordset, 5 Poles, L-Coded, Female (Straight) to Male (90°), 14 AWG, Gray TPU WSOR Cable, 5.0m (16.40') Length |
| IP Rating | IP67 |
| Product Name | Micro-Change (M12) |
| Type | Double Ended |
| UPC | 193264522804 |

### Agency

| | |
|---|---|
| UL | E152210 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 16.0A |
| Voltage - Maximum | 63V AC/DC |

### Physical

| | |
|---|---|
| Cable Diameter | 11.30mm (.445") |
| Cable Length | 5.0m (16.40') |
| Color - Cable Jacket | Gray |
| Connector End A | Micro-Change (M12) |
| Connector End B | Micro-Change (M12) |

Downloaded from Arrow.com.

| | |
|---|---|
| Coupling Style | Threaded |
| Gender | Female-Male |
| Keyway | L-Coded |
| LED Indicator | None |
| Material - Cable Jacket | WSOR TPU |
| Material - Connector Body | TPE |
| Material - Contact | Brass |
| Material - Coupling Nut | Nickel-plated Brass |
| Material - O-Ring | FKM |
| Material - Plating Mating | Gold |
| Net Weight | 1139.001/g |
| Orientation | 90° to Straight |
| Poles | 5 |
| Temperature Range - Operating | -25° to +85°C |
| Wire/Cable Type | UL 21215 |
| Wire Size (AWG) | 14 |



Downloaded from Arrow.com.