

Product data sheet

Specifications



APC NetShelter CX, 24U,
Soundproof Server Rack
Enclosure, 100V to 120V, White,
1275H x 750W x 1130D mm

AR4024X432

! Discontinued

! Discontinued on: Jun 30, 2023

Overview

| | |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|
| Presentation | Specialized enclosures with integrated cooling, noise dampening, and power distribution for server and network applications in office environments. |
| Lead time | Special Order - Call for Quoted Lead Times |

Main

| | |
|---------------------------|---------------------------------------------------------------------------------------------------------------|
| Product or Component Type | Rack enclosure |
| Main Input Voltage | 115 V 120 V |
| Main Output Voltage | 100 V 120 V |
| Input Connection Type | NEMA 5-15P |
| output connection type | 12 NEMA 5-15R |
| Number of rack unit | 24U |
| Provided equipment | Casters Installation guide Key(s) Leveling feet Rack Power Distribution Unit (PDU) Side Panels |

Physical

| | |
|----------------------------|-------------------------------|
| Height | 50.20 in (127.5 cm) |
| Width | 29.53 in (75 cm) |
| Depth | 44.49 in (113 cm) |
| Net Weight | 340.6 lb(US) (154.5 kg) |
| Color | White |
| Mounting preference | No preference |
| Mounting Mode | Not rack-mountable |
| Maximum Mounting Depth | 34.65 in (88.01 cm) |
| minimum mounting depth | 28.35 in (72.01 cm) |
| Rack Width | 19" |
| Permanent permissible load | 1771 lb(US) (803.3 kg) static |

Input

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-----------------|----------|
| Input Frequency | 50/60 Hz |
|-----------------|----------|

Conformance

| | |
|------------------------|----------------|
| Product Certifications | TAA compliance |
| Standards | EIA-310D |

Ordering and shipping details

| | |
|------|--------------|
| GTIN | 731304298205 |
|------|--------------|

Packing Units

| | |
|------------------------|-------------------------|
| Unit Type of Package 1 | PCE |
| Nbr. of units in pkg. | 1 |
| Package 1 Height | 58.66 in (149 cm) |
| Package 1 Width | 47.24 in (120 cm) |
| Package 1 Length | 31.50 in (80 cm) |
| Package weight(Lbs) | 400.6 lb(US) (181.7 kg) |

Contractual warranty

| | |
|----------|--------------------------------|
| Warranty | 2 year (manufacturer's defect) |
|----------|--------------------------------|



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

| Materials and Substances | |
|-----------------------------------|------------------------------------------------------------|
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |

Use Again

| Repack and remanufacture | |
|--------------------------|-----|
| Take-back | Yes |

Image of product / Alternate images

Alternative





