



Part Number : [1301370087](#)

Product Description : Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, Cord Clamp, Duplex Cover Plates only

Series Number : 130137

Status : Active

Product Category : Power Distribution

Engineering Part Number : 3000

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power Distribution
Series	130137
Description	Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, Cord Clamp, Duplex Cover Plates only
Enclosure Rating	NEMA 4
NEMA Configuration	N/A
Product Name	Super-Safeway
Type	Multiple Outlet Box
UPC	78678875050

Agency

UL	E46237
----	--------

Electrical

Current - Maximum per Contact	Per Cust. Supplied Receptacle
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	Per Cust. Supplied Receptacle

Physical

Cord Diameter	8.26-16.64mm (.325-.655")
Cord Grip Body Size	F3 3/4"
Cord Length	N/A
Cord Type	N/A
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber

Mounting Style	Portable
Net Weight	420.026/g
Number of Receptacles	2 - Customer Supplied
Packaging Type	Carton
Receptacle Type	Duplex

This document was generated on May 21, 2026