

Left Side
Connector(s): LC-Duplex Secure
Mode: MM
Housing Color: Yellow
Geom. Spec: N/A

Fiber Path


A - _____ - Fiber B
B - _____ - Fiber A

Notes:

- 1 OM3 assemblies tested at 850nm, all other multimode tested at 1300nm
- 3 Label 2 will not be present on any cable assembly less than 5 meters long.
- 4 Includes dust caps (not shown on print).

Right Side

Connector(s): MT-RJ (No Pins)
Mode: MM
Housing Color: Black
Geom. Spec: 115-1215



VIEW D-D
NOT TO SCALE

A1	Rev Per EC#	RELEASE	2/21/2011	-	D				
P	LTR	REVISION RECORD	DATE	DIN	AF				

DIMENSIONS:
meters

Restricted To:

QTY Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
QTY Doug Kirsch		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
AP'D Doug Kirsch					
NAME FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex Secure to MT-RJ (No Pins)					
SCALE NTS	SIZE A2	DRAWING NO C-1906990	SHEET 1 of 3	REV A1	

LOC	
CE	
DIST	
16	

	A1	Rev Per EC# RELEASE	2/21/2011	-	DH
P	LTR	REVISION RECORD	DATE	D/M	AP

Qty	U of M	Description	Item No
2	piece	Trace Label	14
2	piece	Eyelet/Shrink tube assembly - White	13
1	piece	MT-RJ TwinZip Bend Limiting Boot, Beige	12
1	piece	MT-RJ FERRULE, THERMOPLAST,MM	11
AR	meter	2 fiber, 50/125, 1.8mm, Twinzip, Yellow, OFNP (Plenum)	10
2	piece	LC Connector Assy, 1.6mm-2.0mm, MM	9
1	piece	LC Duplex clip, black	8
2	piece	LC, SC, FC Straight Boot, Beige	7
1	piece	CRIMP EYELET, MT-RJ	6
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	5
1	piece	PIN KEEPER, 3.8MM	4
1	piece	SPRING, MT-RJ, 3.8 DESIGN	3
1	piece	DUST COVER, MT-RJ	2
1	piece	HOUSING, CONN. MT-RJ.BLACK	1

DIN Cable Assy Configurator		WATERL -		HEAT TREAT	
OK Doug Kirsch		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD Doug Kirsch					
NAME FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex Secure to MT-RJ (No Pins)					
SCALE NTS	SIZE A2	DRAWING NO C- 1906990		SHEET 2 of 3	REV A1

