
Part Number : 1300610278
Product Description : BradPower A-Size (7/8”–M22) Single Ended Cordset, 3 Poles, Male (Straight) to Pigtail, 14 AWG, Black TPE Cable, Red Overmold, 2.0m (6.56') Length
Series Number : 130061
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 103006K20M020E



Documents and Resources

Drawings

1300610278_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	130061
Description	BradPower A-Size (7/8”–M22) Single Ended Cordset, 3 Poles, Male (Straight) to Pigtail, 14 AWG, Black TPE Cable, Red Overmold, 2.0m (6.56') Length
IP Rating	IP67
Product Name	BradPower A-Size
Type	Single Ended
UPC	78172562751

Agency

UL	E258922

Electrical

Current - Maximum per Contact	20.0A
Voltage - Maximum	600V

Physical

Cable Diameter	8.63mm (.340")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Connector End A	BradPower A-Size (7/8”–M22)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail

Downloaded from Arrow.com.

Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	252.000/g
Orientation	Straight to Pigtail
Poles	3
Temperature Range - Operating	-20° to +90°C
Wire/Cable Type	TC-ER
Wire Size (AWG)	14

Downloaded from Arrow.com.