Part Number : 1300940530
Product Description : Support Grips for Fiber Optics, Closed Mesh, Single Eye, Bale Length 3", Cable Diameter 5.84-8.13mm (.230-.320"), Approximate Break Strength 136.08kg (300 lbs)
Series Number : 130094
Status : Not Recommended For New Design
Product Category : Cable Grips
Engineering Part Number : 36681



Documents and Resources

Drawings

1300940530_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Not Recommended For New Design
Category	Cable Grips
Series	130094
Description	Support Grips for Fiber Optics, Closed Mesh, Single Eye, Bale Length 3", Cable Diameter 5.84-8.13mm (.230-.320"), Approximate Break Strength 136.08kg (300 lbs)
Product Name	Fiber Optic
Type	Support Grip
UPC	78678836681

Agency

CSA	LR32159

Physical

Approximate Break Strength	136.08kg (300 lbs)
Bale Length	0.076m (3.00")
Body Style	Straight
Cable Diameter	5.84-8.13mm (.230-.320")
Color - Grommet	Orange
Eye Type	Single
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.064m (2.50")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

Downloaded from Arrow.com.