Pushing Performance
Since 1945

RJ45 Plug Stewart




Image is for illustration purposes only. Please refer to product description.

Part number	09 12 000 9957
Specification	RJ45 Plug Stewart
HARTING eCatalogue	https://harting.com/09120009957

Identification

Category	Inserts
Element	Data connectors
Specification	for Han® RJ45 module

Version

Gender	Male
Number of contacts	8

Technical characteristics

Conductor cross-section (AWG)	AWG 24 ... AWG 22
Limiting temperature	-40 ... +85 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	10
Net weight	3 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140016385
eCl@ss	27440218 Module for industrial connectors (data)
ETIM	EC000438
UNSPSC 24.0	39121552

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.