



DIMENSION RANGE	TOLERANCE
0.0m – 1.0m	+10/0 mm
>1.0m – 3.0m	+30/0 mm
>3.0m – 5.0m	+50/0 mm
>5.0m – 10.0m	+100/0 mm
>10.0m	+200/0 mm

DEVELOPMENT, RESEARCH, AND DESIGN

[illegible]