TE Connectivity: Every Connection Counts
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

TERMINALS & SPLICES

MAGNET WIRE TERMINALS



✔ Active

**TE CONNECTIVITY (TE)**

# MAG-MATE CONTACT .187,WITH SOLDER PIN

Magnet Wire Terminals & Splices | MAG-MATE

1534682-1
TE Internal Number: 1534682-1

EU RoHS Compliant
EU ELV Compliant

**Terminal Type** Solder Post
**Magnet Wire Size (mm)** .36 – .45
**Magnet Wire Size (AWG)** 27 – 25
**Material Thickness (in)** .0126
**Packaging Method** Reel, Reel/Carton

**3D PDF**

## DOCUMENTATION

CAD Files

**3D PDF**
PDF
**3D**

**Customer View Model**
2D_DXF.ZIP
**English**

**Customer View Model**
3D_IGS.ZIP
**English**

**Customer View Model**
3D_STP.ZIP
**English**

Downloaded from Arrow.com.

Catalog Pages/Data Sheets

**Magnet Wire Terminals & Splices**

PDF

**English**

**CAVITY FOR MAG-MATE CONTACT WITH SOLDER PIN**

PDF

**English**

Product Specifications

Product Specification

**MAG-MATE Standard Series 187 And 300 Terminals**

PDF

**English**

## FEATURES

Please review product documents or contact us for the latest agency approval information.

Contact Features

**Terminal Type** Solder Post

Dimensions

**Magnet Wire Size (mm)** .36 – .45
**Magnet Wire Size (AWG)** 27 – 25
**Material Thickness (in)** .0126

Packaging Features

**Packaging Method** Reel, Reel/Carton

## PRODUCT COMPLIANCE

Statement of Compliance

**Statement of Compliance**

PDF

Downloaded from Arrow.com.