

Representative Image

Catalog No. 5347

Description: 2 IN INSUL 45 DEGREE LIQ TIGHT CONN

UPC No 786210053479

Home > Cable Protection Systems > T&B Liquidtight Fittings > Liquid tight connectors

2 Inch 45 Degree Malleable Iron Insulated Liquidtight Connector

Descriptors

Category	Liquid tight connectors
Application	Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.

Specifications

Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

Classifications

Brand Name	T&B Liquidtight Fittings
Standard	UL E23018, CSA

Dimensions

Size	2 Inch

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other

by ABB

Downloaded from Arrow.com.

ETIM	EC001180 Screw connection for protective metallic hose
One-piece	N
Material housing	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	2884	441202	N/A	2404630_2020-08-31	N/A
CSA	4484	441202	N/A	2206188	N/A
UL	E23018	N/A	DWTT	N/A	N/A

Downloaded from Arrow.com.