





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/13/06	
A		PART REVISION	4/19/06	
B		ADDED DIM.	3/18/15	AY/RT
C		UPDATE DRAWING	4/13/18	AY/MY



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Natural

Electrical:

Rated Voltage: 250V AC/DC

Rated Current: 3A AC/DC

Contact Resistance: 20 mohms max.

Insulation resistance: 1,000 Mohms min.

Withstand voltage: 1000V AC for 1 minute.

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant

Positions: 2 thru 20

A = .098 [2.50] x No. of Spaces

B = .098 [2.50] x No. of Positions + .091 [2.30]

C = .098 [2.50] x No. of Positions + .028 [0.70]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	LFJ	4/13/06
CHECKED		
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
WIRE TO BOARD PITCH: 2.5MM
CRIMP HOUSING STRAIGHT TYPE

SIZE X	PART NO. 25CH-B-XX	REV. C
REF: S00124T	SCALE: NTS	SHEET 1 OF 1