Part Number : 191640043
Product Description : Perma-Seal Step Down Butt Splice from 14/16 to 18/22 AWG Wire, Carton
Series Number : 19164
Status : Active
Product Category : Splices
Engineering Part Number : SBA-631



Documents and Resources

Drawings

191640043_sd.pdf

Specifications

PS-19902-011-001.pdf

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Splices
Series	19164
Description	Perma-Seal Step Down Butt Splice from 14/16 to 18/22 AWG Wire, Carton
Comments	Step down: 14/16 to 18/22 AWG
Product Name	Perma-Seal
Style	Step Down
Type	Butt Splice
UPC	800753113282

Electrical

Voltage - Maximum	600V

Physical

Barrel Type	Closed
Color - Resin	Blue
Insulation	NiAc
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	NiAc
Net Weight	1.800/g
Packaging Type	Carton
Temperature Range - Operating	-10° to +105°C
Wire Insulation Diameter	4.95mm max.

Downloaded from Arrow.com.

Wire Size (AWG)	14, 16, 18, 20, 22
Wire Size mm^2	0.324-2.08

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Industrial Terminals, 22-10 AWG (see ATS)	640017400
Power Crimp Tool Head for Terminals 22-10 AWG Wire	640057400
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	640160041

Downloaded from Arrow.com.