

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370101](#)
Status: **Active**
Overview: [Watertite® Wet-Location Wiring Solutions](#)
Description: Super-Safeway® Multiple Outlet Box, Standard Depth, 2-Sided, NEMA 5-15 Duplex Receptacles, Cord Clamp, Duplex Cover Plates, 1.83m (6.0') Cord Length, 14/3 SOOW Cord, 5-15 Plug



Documents:
[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification	
CSA	LR6837
UL	E38085
General	
Product Family	Power Distribution
Series	130137
Enclosure Rating	N/A
GFCI Reset	N/A
Mounting Style	Portable
Open Neutral Relay	N/A
Overview	Watertite® Wet-Location Wiring Solutions
Product Literature Order No	987650-7737
Product Name	Super-Safeway™
Receptacle Type	Duplex
Type	Multiple Outlet Box
UPC	78678879603
Woodhead	Yes
Physical	
Cord Diameter	13.59mm (.535")
Cord Grip Body Size	Double C-Clamp
Cord Length	1.83m (6.0')
Feed-Thru	No
Flip Lid	No
Material - Housing	Rubber
Number of Receptacles	2
Packaging Type	Carton
Electrical	
Cord Type	14/3 SOOW
Current - Maximum per Contact	15.0A
GFCI	No
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-15
Voltage - Maximum	120V
Material Info	
Old Part Number	3000-1L143

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
Need more information on product environmental compliance?	
Email productcompliance@molex.com Please visit the Contact Us section for any non-product compliance questions.	
China ROHS	Not Reviewed
ELV	Not Reviewed

Search Parts in this Series
[130137](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION