

Representative Image

Catalog No. TY529MX

Description: CBL TIE 120LB 30IN UV BLACK NYLON

UPC No 786210838908

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications , Length of 762mm (30. Inches), Width of 6.86mm (0.27 Inches), Tensile Strength Rating of 534 Newtons (120 pounds),

Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	Black
Lock Mechanism	Stainless Steel Barb
Tensile Strength	120 pounds , 530 newtons

Classifications

Brand Name	Ty-Rap

Dimensions

Width	0.273 in , 6.93 mm
Length	30.34 in , 770.61 mm
Thickness	0.06 in , 1.52 mm
Bundle Diameter	0.236 to 9.01 in , 6 to 229 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

by ABB

Downloaded from Arrow.com.