2.40 mm Cable Assemblies

RF047-A, RF085, RF086, RF23C



SERIES	END 1 CONNECTOR	END 2 CONNECTOR	OVERALL LENGTH

RF047-A
= (1.2 mm) .047" overshield DIA 29 AWG millimeter wave cable

RF086
= (2.18 mm) .086" overshield DIA 23 AWG millimeter wave cable

RF085
= (2.16 mm) .085" overshield DIA 24 AWG millimeter wave cable

RF23C
= MWC-2350CU-01 millimeter wave cable with copper foil shield

–24SJ
= 2.40 mm Straight Jack

–24SP
= 2.40 mm Straight Plug

–"XXXX"
= Overall Length in millimeters

–0100 (100 mm) 3.94" minimum

VSWR

RF047-A: 1.35 max.
RF086: 1.40 max.
RF085: 1.40 max.
RF23C: 1.40 max.

ALSO AVAILABLE

1.00 mm, 1.35 mm, 1.85 mm, 2.92 mm, SMPM, SMP, SMP3, SMA = RF047-A

1.85 mm, 2.92 mm, SMPM, SMP, SMA = RF086

2.92 mm = RF085

2.92 mm, SMPM, SMP, SMA = RF23C

NITROWAVE® CABLES

• LL043

2.40 mm Board Connectors

240

Cable Mates:
RF047-A, RF086, RF085, RF23C, LL043



240	GENDER	TYPE	PLATING	ORIENTATION	TERMINATION	OPTION	PACKAGING

–J
= Jack

–P
= PCB Mount

–EP
= 50 µ" (1.27 µm) Gold center contact, Passivated outer contact

–ST
= Straight

–CM
= Compression Mount Stripline

–CMM
= Compression Mount Microstrip

–EL
= Edge Launch

–ELW
= Edge Launch Wide


–1
= Without Screws (–CM & –CMM only)

–2
= With Screws (–CM & –CMM only)


–01
= .040" to .100" PCB thickness (–EL & –ELW only)


Leave blank for individually bagged

–B
= Bulk packaged




–CM





–CMM



–EL & –ELW

TERMINATION	A	B
–EL	(9.52) .375	(5.84) .230
–ELW	(12.70) .500	(9.53) .375

2.40 mm Cable Connectors

PRF24





CONNECTORS FOR INDUSTRY STANDARD CABLES	
PRF24-J-C-EP-085-SS	Harbour SS405
PRF24-J-C-EP-405-BS	RG 405
PRF24-P-C-EE-085-SD	Harbour SS405
PRF24-P-C-EP-120A-SS	Semflex HP120
PRF24-J-C-EP-160-SS	Semflex HP160
PRF24-P-C-EP-160-SS	Semflex HP160
PRF24-J-C-EP-140B-SS	IW 1401
PRF24-P-C-EP-140B -SS	IW 1401
PRF24-J-C-EP-150B-SS	IW 1501
PRF24-J-C-EP-150-SS	Dynawave DF150
PRR24-J-C-EP-086-SS	Temp-Flex 1001935086
PRF24-P-C-EP-086-SS	Temp-Flex 1001935086

For a complete list of 2.40 mm cable connectors, visit www.samtec.com?PRF24

P-C = Cable Plug
J-C = Cable Jack
EE = Plating (50 µ" gold center contact & outer contact)
EP = Plating (50 µ" gold center contact, passivated outer contact)
SS = Straight, Solder Clamp
SD = Straight, Direct Solder
BS = Bulkhead, Solder Clamp

INTERFACE STANDARD





Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.

Downloaded from Arrow.com.