

[Home](#)> [5977702607F](#)

Search For

Part Number



Part Number: **5977702607F**

General Description	
Series	597
Configuration	1210 Package
Description	SMD LED 1210 R/G 7" Reel
Package Options	Tape and Reel
Lamp Type	Bi- Color
Lens Color	Non - Diffused

Absolute Maximum Ratings (Ta = 25Â°)	
Reverse Current	100 @ Vr =4V
Derating	from 50Â° @ .6mA/Â°C
Solder Temperature	260Â° fo 5 sec
Operating Temperature	- 55~+100
Storage Temperature	- 55~+100

Operating Characteristics		
Color	Red	Green
Luminous Intensity Min	3.6	9
Luminous Intensity Typical	6.3	16
Luminous Intensity Max	9	23
Dominant Wavelength Typical	653nm	575nm
Power Dissipation Max	100mW	100mW



5977702607F

check stock 



[This is a
RoHS Compliant Product](#)
[To learn more click here](#)