
# Aluminum Chassis *1444 Series*

**Aluminum Body, Walnut Side Option**







Classic

RoHS

## Key Features:

- Spot welded - heavy duty construction chassis.
- Natural aluminum finish (as shown above) - also available in painted steel with walnut side panels).
- Side panels are made from solid walnut and routed out to fit over ends of chassis (pre-punched for easy mounting).
- Walnut side panels attach with four machine screws & lockwashers (included) into metal inserts to avoid wood damage. Screws should not be torqued past 4.43 lbf.in ( 50 cN.m).
- Usable surface of chassis front, back and top are reduced by roughly 7/8” (22 mm) due to inset in walnut sides.
- Optional bottom plates are punched with 4 holes – 3/16” diameter.
- Bottom plate hardware not provided, please order separately - Part number **1421J6** (Pkg. of 6, 6-32 Philips head screws).
- NOTE: our steel chassis covers (1451 series) are NOT compatible with this series.

## Photo Features





Six sizes available with walnut sides.



Standard version shown inside and out.

Downloaded from Arrow.com.



Optional bottom panels available for all sizes.



Protective covering on aluminum is perfect as a layout tool.

## Accessories

- Sheet Metal Screws

## Part Numbers

| Chassis | Chassis w/ Walnut Sides | Aluminum Thickness | Width | Depth | Height | Bottom Plate |
|---|---|---|---|---|---|---|
| **1444-6** | | 0.04 | 4.00 | 4.00 | 2.00 | **1434-6** |
| **1444-45351** | | 0.04 | 4.50 | 3.50 | 1.00 | **1434-4535** |
| **1444-542** | | 0.04 | 5.00 | 4.00 | 2.00 | **1434-54** |
| **1444-6415** | | 0.04 | 6.00 | 4.00 | 1.50 | **1434-8** |
| **1444-8** | | 0.04 | 6.00 | 4.00 | 2.00 | **1434-8** |
| **1444-643** | | 0.04 | 6.00 | 4.00 | 3.00 | **1434-8** |
| **1444-12** | **1444-12CWW** | 0.04 | 7.00 | 5.00 | 2.00 | **1434-12** |
| **1444-753** | | 0.04 | 7.00 | 5.00 | 3.00 | **1434-12** |
| **1444-772** | | 0.04 | 7.00 | 7.00 | 2.00 | **1434-77** |
| **1444-9** | | 0.04 | 8.00 | 4.00 | 1.00 | **1434-10** |
| **1444-10** | | 0.04 | 8.00 | 4.00 | 2.00 | **1434-10** |
| **1444-84515** | | 0.04 | 8.00 | 4.50 | 1.50 | **1434-845** |
| **1444-862** | | 0.04 | 8.00 | 6.00 | 2.00 | **1434-86** |
| **1444-14** | | 0.04 | 9.00 | 5.00 | 2.00 | **1434-14** |
| **1444-972** | | 0.04 | 9.00 | 7.00 | 2.00 | **1434-97** |
| **1444-9552** | | 0.04 | 9.50 | 5.00 | 2.00 | **1434-955** |
| **1444-95525** | | 0.04 | 9.50 | 5.00 | 2.50 | **1434-955** |
| **1444-9553** | | 0.04 | 9.50 | 5.00 | 3.00 | **1434-955** |
| **1444-1053** | | 0.04 | 10.00 | 5.00 | 3.00 | **1434-105** |
| **1444-15** | | 0.04 | 10.00 | 6.00 | 1.00 | **1434-16** |
| **1444-16** | **1444-16CWW** | 0.04 | 10.00 | 6.00 | 2.00 | **1434-16** |
| **1444-10825** | | 0.04 | 10.00 | 8.00 | 2.50 | **1434-108** |
| **1444-1172** | | 0.04 | 11.00 | 7.00 | 2.00 | **1434-117** |
| **1444-1273** | | 0.04 | 12.00 | 7.00 | 3.00 | **1434-127** |
| **1444-22** | **1444-22CWW** | 0.05 | 12.00 | 8.00 | 2.00 | **1434-22** |
| **1444-12825** | | 0.05 | 12.00 | 8.00 | 2.50 | **1434-22** |
| **1444-24** | **1444-24CWW** | 0.05 | 12.00 | 8.00 | 3.00 | **1434-22** |
| **1444-29** | | 0.05 | 12.00 | 10.00 | 2.00 | **1434-29** |
| **1444-12103** | | 0.05 | 12.00 | 10.00 | 3.00 | **1434-29** |
| **1444-12123** | | 0.05 | 12.00 | 12.00 | 3.00 | **1434-1212** |
| **1444-1372** | | 0.04 | 13.00 | 7.00 | 2.00 | **1434-137** |
| **1444-18** | | 0.04 | 13.50 | 5.00 | 2.00 | **1434-18** |
| **1444-1463** | | 0.05 | 14.00 | 6.00 | 3.00 | **1434-146** |
| **1444-14103** | | 0.05 | 14.00 | 10.00 | 3.00 | **1434-1410** |
| **1444-1573** | | 0.05 | 15.00 | 7.00 | 3.00 | **1434-157** |
| **1444-1593** | | 0.05 | 15.00 | 9.00 | 3.00 | **1434-159** |
| **1444-26** | | 0.05 | 16.00 | 8.00 | 2.00 | **1434-26** |
| **1444-28** | | 0.05 | 16.00 | 8.00 | 3.00 | **1434-26** |
| **1444-20** | | 0.04 | 17.00 | 4.00 | 3.00 | **1434-20** |
| **1444-1763** | | 0.05 | 17.00 | 6.00 | 3.00 | **1434-176** |
| **1444-1773** | | 0.05 | 17.00 | 7.00 | 3.00 | **1434-177** |
| **1444-1783** | | 0.05 | 17.00 | 8.00 | 3.00 | **1434-178** |
| **1444-30** | | 0.05 | 17.00 | 10.00 | 2.00 | **1434-30** |
| **1444-32** | **1444-32CWW** | 0.05 | 17.00 | 10.00 | 3.00 | **1434-30** |
| **1444-33** | **1444-33CWW** | 0.05 | 17.00 | 10.00 | 4.00 | **1434-30** |
| **1444-17105** | | 0.05 | 17.00 | 10.00 | 5.00 | **1434-30** |

Downloaded from Arrow.com.

| Chassis | Chassis w/ Walnut Sides | Aluminum Thickness | Width | Depth | Height | Bottom Plate |
|---|---|---|---|---|---|---|
| **1444-17123** | | 0.05 | 17.00 | 12.00 | 3.00 | **1434-1712** |
| **1444-17132** | | 0.05 | 17.00 | 13.00 | 2.00 | **1434-1713** |
| **1444-17133** | | 0.05 | 17.00 | 13.00 | 3.00 | **1434-1713** |
| **1444-17134** | | 0.05 | 17.00 | 13.00 | 4.00 | **1434-1713** |
| **1444-17135** | | 0.05 | 17.00 | 13.00 | 5.00 | **1434-1713** |
| **1444-17143** | | 0.05 | 17.00 | 14.00 | 3.00 | **1434-1714** |
| **1444-17154** | | 0.05 | 17.00 | 15.00 | 4.00 | **1434-1715** |
| **1444-17156** | | 0.05 | 17.00 | 15.00 | 6.00 | **1434-1715** |
| **1444-17173** | | 0.05 | 17.00 | 17.00 | 3.00 | **1434-1717** |
| **1444-17174** | | 0.05 | 17.00 | 17.00 | 4.00 | **1434-1717** |

Tags: **chassis**, **aluminum chassis**, **classic**, **vintage**, **tube**, **audio**

*Data subject to change without notice.*

© 2026. Hammond Manufacturing Ltd. All rights reserved.

Downloaded from Arrow.com.