



Part Number : 1054170334

Series Number : 105417

Product Category : Crimp Terminals

Product Description : Mega-Fit Crimp Terminal, Male, Tin (Sn) Plating, Double 20+20, 18+18 or Single 16-14 AWG, Reel

Status : Active

Documents & Resources

Drawings

Drawing 1054170334_sd.pdf

Packaging Design Drawing 1054170100-000.pdf

Specifications

Application Specification 768232000-AS-000.pdf

Product Specification 1054171000-PS-000.pdf

Product Specification 1054171000-PS-CH-000.pdf

Product Specification 1054171000-PS-KO-000.pdf

Product Specification 1054171000-PS-SPA-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	105417
Description	Mega-Fit Crimp Terminal, Male, Tin (Sn) Plating, Double 20+20, 18+18 or Single 16-14 AWG, Reel
Application	Power, Wire-to-Wire
Product Family	Mega-Fit Power Connectors
Product Name	Mega-Fit
UPC	191130081318

Electrical

Current - Maximum per Contact	21.0A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Durability (mating cycles max)	25
Gender	Male
Material - Metal	High Conductivity Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.330/g
Packaging Type	Reel
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.15-3.58mm max.
Wire Size (AWG)	14, 16, 18+18, 20+20
Wire Size mm ²	1.50-2.50

Use with Part(s)

Description	Part Number
Mega-Fit Free Hanging Dual Row Plug Housings	<u>105411</u>
Mega-Fit Single Row Plug Housings	<u>213814</u>
Mega-Fit Single Row Plug Housings	<u>213815</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Mega-Fit Crimp Terminals, 14-16 AWG	<u>2002221200</u>
Hand Crimp Tool for Mega-Fit Crimp Terminals, 14 AWG, UL1007 and UL1015 Wire	<u>2133091300</u>
Hand Crimp Tool for Mega-Fit Crimp Terminals, 16 AWG, UL1007 and UL1015 Wire	<u>2133091400</u>
FineAdjust Applicator for Mega-Fit Crimp Terminals, 14-16 AWG, UL1015 Wire	<u>639043500</u>
FineAdjust Applicator for Mega-Fit Crimp Terminals, 14-16 AWG, UL1007 Wire	<u>639043600</u>

This document was generated on Sep 09, 2024