

# PTEL2R

APC Surge Module for Analog Phone Line,  
Replaceable, 1U, use with PRM4 or PRM24  
Rackmount Chassis



## Overview

Lead time	Usually in Stock
-----------	------------------

## Physical

Colour	Black
Depth	6.9 cm
Height	4.4 cm
Net weight	0.02 kg
Width	1.9 cm

## Output

Number of power socket outlets	1
--------------------------------	---

## Conformance

Product certifications	CUL recognized CE
Standards	UL 497A

## Environmental

Ambient air temperature for operation	-15...45 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...3048.00 m

## Surge Protection and Filtering

Data line protected	Dual analog line (4 wire)
Response time	1 ns common mode
Peak current	0.25 kA common mode 0.2 kA normal mode
Data line protection	RJ45 analog phone line for phone/fax/modem/DSL

## Packing Units

Package 1 Weight	0.05 kg
Package 1 Height	9.9 cm
Package 1 width	3.3 cm
Package 1 Length	9.5 cm
SCC14	30731304202852
Number of Units in Package 2	96
Package 2 Weight	6.70 kg
Package 2 Height	206.38 mm
Package 2 width	412.75 mm
Package 2 Length	638.18 mm
Number of Units in Package 3	28

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	Lifetime
----------	----------