Datasheet for part number DBA-25S-A197-F0

Our Catalog Part Number: DBA-25S-A197-F0
Our Global Manufacturing Part Number: 119998-0357
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*A

Product Datasheet	
General	Crimp Connector without contacts
Wire Gauge Range AWG	AWG 20-28
Mating Cycles	50, 200
Dielectric Withstanding Voltage	500 VAC at sea level
Current Rating	5 A max
Contact Resistance	15 milli Ohm max
Operating Temperature	-55°/+105°
Salt Spray Test	12 hours
Shell Material	steel
Shell Finish	Yellow chromate over zinc
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Contact Arrangement	25 contacts size 20
Gender	Socket
Contacts	delivery without contacts, please order separately
Available contacts Size 20 Female:	AWG 20-24: A191: 980-2002-304 / 400 per Reel Gold flash (class 3): 980-200-923 / 5000 per Reel A191 (class 2): 980-200-943 / 5000 per Reel
Contact Type	stamped
Contact Material	copper alloy
Contact Finish	gold over nickel
Contact Termination	Crimp
Mounting Methode	.120" (3,05mm) Through Hole

Specifications and dimensions subject to change.

Downloaded from Arrow.com.