

Honeywell Sensing and Control

Search 

narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6165)
- Switches (9781)
- Wireless (45)

Technology

- Control and Instrumentation (890)
- Electromechanical (9307)
- Magnetic (541)
- Platinum thin film (56)
- Thick Film (1372)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

[find out more](#) 

white papers

- ▶ Wireless Switches Offer Unlimited Benefit
- ▶ Basic Switches Are Not Created Equal
- ▶ Applying Precision Switches
- ▶ Sensors for Medical Devices
- ▶ New Ways to Measure Torque
- ▶ Choosing Safety Switches
- ▶ Specifying Hour Meters

Need help?

[Click here to contact us](#) 

BM-1RD33-A2

(Home : Products : Switches » MICRO SWITCH™ Basic Switches » Premium Large Basic Switches » BZ/BA/WA/YZ)



Actual product appearance may vary.
[click here to download Hi-Res image](#)

BM Series Standard Basic Switch, Single Pole Double Throw Circuitry, 22 A at 250 Vac, Overtravel Plunger Actuator, 1.95 N to 2.78 N [7.0 oz to 10.0 oz] Operating Force, Silver Contacts, Screw Termination, UL, CSA, CE, ENEC

[Sales & Service](#) [Distributor Inventory](#) [Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Switch Type	MICRO SWITCH™ Standard 25.4 mm H x 17.8 mm W x 50.8 mm L [1.0 in H x 0.7 in W x 2.0 in L]
Sealed	No
Ampere Rating	22 A
Circuitry	SPDT
Actuator	Overtravel Plunger
Termination	Screw
Operating Temperature	-55 °C to 85 °C [-67 °F to 185 °F]
Voltage	250 Vac
Contact Type	Silver
Operating Force (OF)	1.95 N to 2.78 N [7.0 oz to 10.0 oz] max.
Release Force	1.11 N [4.0 oz] min.
Pretravel (PT)	0.38 mm [0.015 in] max.
Overtravel (OT)	1.52 mm [0.060 in] min.
Differential Travel (DT)	0.013 mm [0.0005 in] max.
Operating Position (OP)	21.21 mm ±0.51 mm [0.835 in ±0.020 in]
Material	Plastic
Housing Material	General Purpose Phenolic
Agency Approvals and Standards	UL, CSA, CE, ENEC
Mounting Screw Size	3.53 mm [0.139 in]
Mounting Centers	25.4 mm [1 in]
Tightening Torque	0.33 N m [3.0 in lb]
Weight	28.6 g [0.063 lb]
Package Height	24.1 mm [0.95 in]
Package Width	17.5 mm [0.69 in]
Package Length	49.3 mm [1.94 in]
Recommended For	Added overtravel, for manual operation and slow 20 ° max. cam rise
Comment	CE: 61058-1; UL: E12252; CSA: LR41370; Bottom facing #6 screws and cupwashers
Availability	Global
UNSPSC Code	30211905
UNSPSC Commodity	30211905 Snap switches
Series Name	BZ/BA/WA/YZ

contacts

- ▶ Customer Service
- ▶ Technical Support
- ▶ Global Sales & Service
- ▶ View Site Demo
- ▶ Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.

- ▶ Meet Dr. Larry

my links

- ▶ Login to iCOM
- ▶ Login to Rep/AD Portal
- ▶ Login to Digital University

News Center

- ▶ Honeywell Introduces TruStability® NSC Series, Uncompensated / Unamplified Board Mount Pressure Sensors
- ▶ HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER
- ▶ HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICs WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT
- ▶ HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION
- ▶ HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO
- ▶ HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION

MICRO SWITCH
Anniversary site