

Specifications



Eaton BSPMA3240DLGR

Eaton Bussmann series BSPM series surge arrester, Technology type MOV, Surge arrester, Thermoplastic, UL94V0, 50/60 Hz, 200 Kilo Ampere, Thermoplastic, Remote Contact

| General specifications | |
|------------------------|--|
| PRODUCT NAME | Eaton Bussmann series BSPM series surge arrester |
| CATALOG NUMBER | BSPMA3240DLGR |
| UPC | 051712709071 |
| PRODUCT LENGTH/DEPTH | 2.13 in |
| PRODUCT HEIGHT | 3.54 in |
| PRODUCT WIDTH | 2.56 in |
| PRODUCT WEIGHT | 0.73 lb |
| WARRANTY | Five year limited warranty |
| COMPLIANCES | Contact factory RoHS Compliant |
| CERTIFICATIONS | UL 94V0 UL Listed |

Product specifications

| | |
|---------------------------|-----------------------|
| TYPE | Surge arrestor |
| SPECIAL FEATURES | Technology type MOV |
| APPLICATION | Surge Protection |
| FREQUENCY RATING | 50/60 Hz |
| NOMINAL DISCHARGE CURRENT | 20 kA |
| OPERATING VOLTAGE | 275 |
| ENCLOSURE | Thermoplastic, UL94V0 |
| SURGE CURRENT | 200 kA |
| INDICATOR TYPE | Remote contact |
| SHORT-CIRCUIT RATING | 200 kA |
| OPERATING TEMPERATURE | -35 to 85 °C |
| MOUNTING METHOD | 35 mm DIN rail |
| DEGREE OF PROTECTION | IP20 |
| MATERIAL | Thermoplastic |

Resources

CATALOGS

[BSPMA3240DLGR~240V Delta, 3P](#)

[Bussmann series complete full line catalog no. 1007](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BSPMA3240DLGR](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

