


 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



 Active

Always EU RoHS/ELV Compliant (Statement of Compliance)

? Contact
? Contact Type = Junior Timer
? Receptacle
? Wire Range = 0.50 -1.40 ² [20-16] mm
[AWG]
? Insulation Diameter = 2.29 - 3.30 mm

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

[RECEPTACLE, MINI - SPRING](#) (PDF, English)

Catalog Pages/Data Sheets:

? None Available

Product Specifications:

? None Available

Application Specifications:

? None Available

Instruction Sheets:

[Heavy Duty Miniature Quick -Change Applicators \(Side -... \(PDF, English\)](#)

CAD Files: ([CAD Format & Compression Information](#))

- ? 2D Drawing (DXF, Version G)
- ? 3D Model (IGES, Version G)
- ? 3D Model (STEP, Version G)

List all Documents

Additional Information:

? Product Line Information

Additional Product Images:

? Line Drawing

Related Products:

? Tooling

Product Features

Product Type Features:

? Product Type = Contact

? Gender = Receptacle

? Insulation Diameter (mm [in]) = 2.29 – 3.30
[0.090 – 0.130]

? Tab Fit (mm [in]) = 2.79 x 0.81 [.110 x .032]

Body Related Features:

? Wire Range (mm [AWG]) = 0.50 - 1.40 ² [20-16]

? Single Wire Sealing System = No

Contact Related Features:

? Contact Type = Junior Timer
 ? Contact Material = Phosphor Bronze
 ? Contact Mating Area Plating Material = Pre -Tin

Industry Standards:

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

? Terminate To = Wire

Packaging Related Features:

? Packaging Method = Strip

Other:

? GET 0.64 Connector System = No

? Brand = AMP