

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- Accessory
- M5
- Guided M8
- M8
- M10.5
- M12 (A)**
- M12 (B)
- M12 (D)
- M12 (I)
- M12 (K)
- M12 (L)
- M12 (S)
- M12 (T)
- M12 (X)
- M23
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



M12A-05PMMT-EE0001

Operating Temperature: -55°C ~ +125°C
 Transmission Speed: N/A
 Shielded: Plastic, Non-shielded
 Jacket Material: N/A
 Certificate: N/A

You must login first for view the price

Quantity

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

M Series, A...	M Series, A...	M Series, A...	M Series, A...	M Series, M12, A...	M Series, M12, A...
APPM-AAAMA012... N/A	APPM-AAAMA012... N/A	APTM-BMZMA012... N/A	APTM-BMZMA012... N/A	M12A-05PFFT... -55°C ~ +125°C	MSAP-05BFFA... -40°C ~ +105°C
<input type="text" value="0"/>	<input type="text" value="0"/>	<input type="text" value="0"/>	<input type="text" value="0"/>	<input type="text" value="0"/>	<input type="text" value="0"/>

Specifications	Download / CAD
Nominal Current 4A	Connector Type SMT
Shielded Plastic, Non-shielded	No. of Contacts 05
Connector Gender Male	Backshell N/A
Mating Style N/A	IP Rating Non-waterproof
Assembly Style SMT 180°	

People Also Bought

