
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

RELAYS, CONTACTORS & SWITCHES

MID-RANGE



✔ Active

TE CONNECTIVITY (TE)

FCA-210-HX4

CII | FCA 10-25 Amp Relay

FCA-210-HX4
TE Internal Number: 2-1617752-7

Not EU RoHS Compliant
Not EU ELV Compliant

Contact Arrangement 2 Form C, DPDT, 2 C/O

Coil Suppression Diode With

Auxiliary Contacts Without

Terminal Plating Tin-Lead

Contact Current Rating (A) 10

PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

FCA-210-HX4
PDF
English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Downloaded from Arrow.com.

Terminal Configuration Solder Pins, 90°
Relay Type Military/Aerospace Mid-Range
Product Type Relay
Enclosure Type Hermetically Sealed

Electrical Characteristics

Coil Suppression Diode With
Coil Voltage Rating (VDC) 28
Coil Resistance (Ω) 320
Back EMF Suppression With
Coil Magnetic System Polarized, Monostable
Shock 200G's, 6ms
Actuating System DC
Vibration 30G's, 33 – 3000Hz

Contact Features

Contact Arrangement 2 Form C, DPDT, 2 C/O
Auxiliary Contacts Without
Terminal Plating Tin-Lead
Contact Current Rating (A) 10
Contact Base Material Silver Cadmium Oxide

Mechanical Attachment

Mounting Type Horizontal Flange Mount

Usage Conditions

Operating Temperature Range (°C) -70 – 125

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.