Part Number : 1212080210
Product Description : mPm DIN Valve Connector, Form B-11mm, External Thread, 2 Pole Plus Ground with A1 Circuit, 24V, Amber LED, Nitrile Gasket, Bulk Pack, Mounted
Series Number : 121208
Status : Obsolete
Product Category : Industrial Connectors
Engineering Part Number : S22200TA1H2RSN



Obsolete

Documents and Resources

Drawings

1212080210_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

PK-121208-S22-001.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Industrial Connectors
Series	121208
Description	mPm DIN Valve Connector, Form B-11mm, External Thread, 2 Pole Plus Ground with A1 Circuit, 24V, Amber LED, Nitrile Gasket, Bulk Pack, Mounted
IP Rating	IP65, IP67
Product Name	mPm
Type	Field Attachable Connector
UPC	884982511286

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	24V

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Form	B - 11mm
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Contact	Brass
Material - Coupling Nut	N/A

Obsolete

Downloaded from Arrow.com.

Material - Plating Mating	Silver
Orientation	90° Angle
Pitch - Mating Interface	11.00mm
Poles	2
Temperature Range - Operating	-40° to +90°C
Wire Size (AWG)	N/A

Obsolete

Downloaded from Arrow.com.