Power Cord C14 to C15 - Heavy-Duty, 15A, 250V, 14 AWG, 3 ft. (0.91 m), Black

MODEL NUMBER: **P018-003**









Connects network hardware with C15 power connections to PDUs and UPS systems with C14 type inputs.

Highlights

- Recommended for powering PoE switches with high-wattage power supplies
- 3 ft. length allows flexibility in placing devices, while avoiding cable clutter
- C14 to C15 power cable replaces or upgrades original manufacturer's power cord
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

Package Includes

P018-003 C14 to C15 Power Cable, 3 ft. (0.9 m), Black

Features

C14 to C15 Power Cord for Network Devices That Require a Heavy-Gauge Connection
This 250V C14 to C15 cable features 14 AWG wire suitable for high power connections, making it reliable for large server applications that require a higher-rated, heavier-gauge cable. The C15 connector is designed for higher-temperature devices, such as electric kettles, PoE (Power over Ethernet) switches with high-wattage power supplies, and similar network components. This IEC C14 to IEC C15 cord can also replace or upgrade the standard power cord provided by the device's manufacturer. The three-foot length helps reduce cable clutter and minimize the risk of tripping.

Features an SJT Jacket and Fully Molded Ends
This computer AC power cable features an SJT jacket and fully molded ends. This gives the cable extra flexibility, reduces stress and ensures long life and durability.

Specifications

OVERVIEW	
UPC Code	037332168436
Product Type	PDU Extension Power Cord
Device Compatibility	Network Switch; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	250
CONNECTIONS	

Downloaded from Arrow.com.

Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C15
Connector Style	Straight
PHYSICAL	
Color	Black
Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.3mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm^2)	2.08
Power Cord Color	Black
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	0.20 x 4.80 x 5.60
Shipping Dimensions (hwd / cm)	0.51 x 12.19 x 14.22
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
Unit Dimensions (hwd / in.)	0.200 x 4.800 x 5.600
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No

Downloaded from Arrow.com.

Locking Power Cord	No
Locking	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Downloaded from Arrow.com.