Specifications







Eaton CPL-4-50TR-R

Eaton CPL inductor, 50 nH, 5 A ISAT, 0.6 mΩ resistance, SMT mounting, Ferrite, 8-pins, Four-phase, 750 qty.

General specifications	
PRODUCT NAME	Eaton CPL inductor
CATALOG NUMBER	CPL-4-50TR-R
UPC	051712825207
EAN	5027590250825
PRODUCT LENGTH/DEPTH	1.417 in
PRODUCT HEIGHT	0.189 in
PRODUCT WIDTH	0.335 in
PRODUCT WEIGHT	0.0125 lb
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
PHASE	Four-phase
ISAT	5 A
PACKAGE QUANTITY	750
MATERIAL	Ferrite
CONTACT CONFIGURATION	Eight-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	0.6 mΩ
INDUCTANCE	50 nH
SERIES	CPL

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CPL-4-50TR-R Eaton CPL CPLA CPLE mutli phase power indcutors data sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.