

Specification Sheet

Part Number: 211-60000



P-Clamps easily guide and locate wire and cables up to 1" in diameter. Designed with a radius edge to prevent chafing and cutting into insulation.

P-Clamp, 0.39" Wide, 0.13" Max Bundle Dia, 0.17" Mounting Hole Dia, PA66HS, Black, 100/pkg

Article Number	211-60000
Type	H1P
Color	Black (BK)
Quantity Per	bag
Product Description	HellermannTyton P-Clamps easily guide and locate wires and cables. The clamps are designed with a radius edges to prevent chafing and cutting into insulation. Available sizes up to 1" bundle diameters.
Short Description	P-Clamp, 0.39" Wide, 0.13" Max Bundle Dia, 0.17" Mounting Hole Dia, PA66HS, Black, 100/pkg
Global Part Name	H1P-PA66HS-BK

Fixation Method	screw-hole
Variant	Closed
Width W (Imperial)	0.39
Width W (Metric)	10.0
Bundle Diameter Max (Imperial)	0.13
Bundle Diameter Max (Metric)	3.2
Nominal Diameter (Imperial)	0.13
Nominal Diameter (Metric)	3.2
Wall Thickness WT (Imperial)	0.031
Wall Thickness WT (Metric)	0.8
Mounting Hole Diameter D (Imperial)	0.17
Mounting Hole Diameter D (Metric)	4.2 mm
Mounting Hole Diameter D Min (Imperial)	0.17
Mounting Hole Diameter D Max (Imperial)	0.17
Mounting Hole Diameter D Max (Metric)	4.2
Mounting Hole Centers (Imperial)	0.33

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988