



Part Number : [1301110054](#)
Product Description : Pro-Yellow Molded Stringlight, 150W, 12/3 STW with 2.74m (9.0') Lead, 10 Sockets with Guards, Overall Length 30.48m (100.0'), with Molded NEMA 5-15 Plug and Connector, cULus Listed
Series Number : 130111
Status : Active
Product Category : Lamps and Lights
Engineering Number : 5038-F



Documents & Resources

Drawings

[1301110054 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130111
Description	Pro-Yellow Molded Stringlight, 150W, 12/3 STW with 2.74m (9.0') Lead, 10 Sockets with Guards, Overall Length 30.48m (100.0'), with Molded NEMA 5-15 Plug and Connector, cULus Listed
NEMA Configuration	NEMA 5-15
NEMA Rating	Rain Tight
Product Name	Pro-Yellow
Type	String Lights
UPC	78172561111

Agency

UL	E112216
----	---------

Electrical

Lamp Wattage - Maximum	150W
Lumens	1500
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Incandescent Base
Cord Length - Primary	2.74m (9.0')
Cord Length - Secondary	0.305m (1.0')

Cord Type - Primary	12/3 STW
Depth	N/A
Duty	Commercial
Guard Included	Yes
Guard Type	Polypropylene
Height	N/A
Lamp Type	A21
Length	30.48m (100.0')
Material - Guard	Polypropylene
Mounting Style	Stringer
Outlet	NEMA 5-15
Packaging Type	Carton
Socket Construction	Molded

This document was generated on Sep 16, 2025