Part Number : 2270040102
Product Description : Sentrality 3.40mm Screw Mount Pin, 16.00mm Length, Bag
Series Number : 227004
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

2270040102_sd.pdf

2032630006-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

2043130018-AS-000.pdf

2043130018-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	227004
Description	Sentrality 3.40mm Screw Mount Pin, 16.00mm Length, Bag
Application	Board-to-Board
Component Type	PCB Header
Product Name	Sentrality
UPC	198282540335

Electrical

Current - Maximum per Contact	75.0A
Voltage - Maximum	600V

Physical

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	3.40mm
Durability (mating cycles max)	200
First Mate / Last Break	No
Gender	Male
Glow-Wire Capable	No
Guide to Mating Part	No

Downloaded from Arrow.com.

Height Above Board	16.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Net Weight	4.049/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PCB Retention	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Screw Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
Sentrality Top-entry Knurled Press-Fit Socket Assemblies with Self-alignment Capability	204313
Sentrality Top-entry Knurled Press-Fit Socket Assemblies	204316
Sentrality Top-entry Surface Mount Socket Assemblies	204318
Sentrality Top-entry Surface Mount Socket Assemblies with Self-alignment Capability	204365
Sentrality Top-entry Surface Mount Socket Assemblies	212194
Sentrality Surface Mount Socket Assemblies	212195
Sentrality 3.40mm Right-Angle Socket Assemblies	205000

Downloaded from Arrow.com.