

6

5

4

3


2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/10/18	



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Plating:

Gold flash over Nickel underplate overall

Electrical:

Current rating: 3 Amp

Contact resistance: 20 mohms max

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 500 VAC

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant



Positions: 06, thru 64

A = .100 [2.54] x No. of Positions per Row + .185 [4.70]

B = .100 [2.54] x No. of Spaces

C = .100 [2.54] x No. of Positions per Row + .035 [0.90]

D = .100 [2.54] x No. of Positions per Row - .050 [1.27]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	HR	1/10/18
CHECKED	YC	1/10/18
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
.100 [2.54] FLAT CABLE IDC SOCKET
STANDARD SINGLE WIPE CONTACTS

SIZE	PART NO.	REV.
X	FCS-C1-XX-G	-

REF: S00111C SCALE: NTS SHEET 1 OF 1

6

5

4

3

2

1