

Cable marker carrier - KMK HP (29X8) - 0830721

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable marker carrier, transparent, Mounting type: Assembly with cable binders, Cable diameter: ≥ 6 mm, Lettering field: 29 x 8 mm



Why buy this product

- ✓ Plastic cable markers for insert labels, for assembly with cable binders
- ✓ Plastic cable markers for marking and bundling conductors and cables indoors
- ✓ The markers have eyelets and are attached with cable binders
- ✓ The marked insert label is protected from dirt by the sealing cap

RoHS

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	100 STK
GTIN	 4 046356 725798
GTIN	4046356725798
Weight per Piece (excluding packing)	2.000 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Width (a)	8 mm
Height	29 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Cable marker carrier - KMK HP (29X8) - 0830721

Technical data

Ambient conditions

Ambient temperature (assembly)	-40 °C
--------------------------------	--------

General

Color	transparent
Components	Halogen-free
Flammability rating according to UL 94	V0
Material	PC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Marking mounting type	Assembly with cable binders

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27400401
eCl@ss 6.0	27149103
eCl@ss 7.0	27400401
eCl@ss 8.0	27149153
eCl@ss 9.0	27144075

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC002248
ETIM 6.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504

