


MODEL NO.	PACKAGING
134-1000-022	ONE PCS PER BAG

REV	ECO	DATE
001	ECO-17-0022	12/18/2017
002	ECO-18-0022	08/21/2018



NOTES: UNLESS OTHERWISE SPECIFIED

- MATERIAL & FINISH:
 - BODY & SHELL: PASSIVATED STAINLESS STEEL
 - CONTACT PIN : GOLD PLATED BERYLLIUM COPPER
 - INSULATOR: ULTEM 1000 AMBER
 - GASKET: SILICONE RED
 - C RING: BERYLLIUM COPPER
- ELECTRICAL:
 - IMPEDANCE: 50 OHMS
 - FREQUENCY RANGE: DC-46.5 GHz
 - DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS MIN
 - VOLTAGE STANDING WAVE RATIO:
 - DC - 4 GHz: 1.05 MAX
 - 4 - 20 GHz: 1.08 MAX
 - 20 - 46.5GHz: 1.15 MAX
 - CONTACT RESISTANCE: CENTER CONTACT: 4 MILLIOHMS MAX
OUTER CONTACT: 2.5 MILLIOHMS MAX
 - INSULATION RESISTANCE: 5000 MOHM MIN
- MECHANICAL:
 - ENGAGEMENT/ DISENGAGEMENT FORCE: 0.23 NM MAX
 - COUPLING PROOF TORQUE: 1.65NM MIN (1.85MM)
 - COUPLING NUT RETENTION FORCE: 267 N MIN
 - CONTACT RETENTION: 20 N MIN
 - DURABILITY: 500 CYCLES MIN
- ENVIRONMENT:
 - THERMAL SHOCK: MIL-STD-202, METHOD 107, CONDITION B.
 - OPERATING TEMPERATURE: -65 TO 165°C
 - SHOCK: MIL-STD-202, METHOD 213, CONDITION I
 - VIBRATION: MIL-STD-202, METHOD 204, CONDITION D
 - MOISTURE RESISTANCE: MIL-STD-202, METHOD 106

Model No. 134-1000-022		Johnson	
RoHS2		Title: ADAPTER ASSEMBLY 1.85mm PLUG TO 2.92mm(SMK) JACK	
2011/REU		Drawing No. 134-1000-022	
XXX + 02		Rev. 002	
XXXX + 01		Date 08/21/2018	
ANGLES 10°		Size C	
		DO NOT SCALE DRAWING	
		NONE	
		Sheet 1 of 1	