




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/23/21	
A		UPDATE TITLE.	6/10/21	
B		UPDATE LABEL	7/19/21	WX/AC
C		UPDATE DESCRIPTION	4/11/23	SS



USB, TYPE C
FEMALE



SPECIFICATIONS:

Material:

Case, cover & Chassis: PPHOX, rated UL94V-1, Color: white
AC Blades: Brass, Nickel plated

Electrical:

Input:

Voltage: 100Vac to 240Vac
Current: 0.5A Max. @ 100Vac input & max load
Frequency: 50Hz / 60Hz

Output Power:

Total Output: 18 Watts max.
PD Output: 5Vdc @ 3A
9Vdc @ 2A
12Vdc @ 1.5A

Load Regulation: $\pm 7\%$

Line Regulation: $\pm 7\%$

(Switching power supply adjust the PD output to match device connected)

Insulation Resistance: 50 Mohms min @ 500VDC

Dielectric withstanding voltage (Hi-pot): 3,000V AC For 1 Minute

Leakage Current: 0.25mA max. @ 240V AC/50Hz


Temperature Rating:

Operating Temperature: -10°C to $+40^{\circ}\text{C}$

Storage Temperature: -20°C to $+85^{\circ}\text{C}$

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X $\pm .10$	$\varnothing$.X $\pm .10$
.XX $\pm .020$	$\varnothing$.XX $\pm .015$
.XXX $\pm .015$	$\varnothing$.XXX $\pm .010$

DRAWN	WX	3/23/21
CHECKED	AC	3/23/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

**ADAM
TECH**

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
AC POWER ADAPTER, NEMA 1-15 TO USB TYPE C
18W PD OUTPUT, COLOR WHITE

SIZE X	PART NO. PA-014	REV. C
-----------	--------------------	-----------

REF: _____ SCALE: NTS SHEET 1 OF 1