







B

A



P.C.B. RECOMMENDED HOLE LAYOUT  
SEEN FROM COMPONENT SIDE  
ALL CENTERLINE DIMENSIONS ARE BASIC.

- NOTES:
- CONNECTOR MATERIALS:  
HOUSING: THERMOPLASTIC UL94 V-0  
CONTACT/SHIELD: COPPER ALLOY  
SHIELD PLATING: NICKEL OR TIN  
CONTACT PLATING: SELECTIVE GOLD IN CONTACT AREA  
SEE CHART FOR PART NUMBER
  - FOR PRODUCT SPECIFICATIONS SEE PR026-01.
  - TOLERANCES COMPLY WITH F.C.C. DIMENSION REQUIREMENTS.
  - PRODUCT DESIGNED FOR CATEGORY 5 APPLICATIONS.

|                          |                |
|--------------------------|----------------|
| 30 MICRO-INCHES [0.76um] | SS-7188VS-A-NF |
| CONTACT PLATING          | PART NUMBER    |

|                                                                                                             |  |                                                                                                                                                                                                                                                                                                                           |                                         |
|-------------------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------|
| THIRD ANGLE PROJECTION<br>                                                                                  |  | <b>Bel Stewart Connector</b><br>11118 Susquehanna Trail South<br>Glen Rock, PA 17327-9199<br>(717) 235-7512 Fax: (717) 235-7954 <a href="http://www.stewartconnector.com">http://www.stewartconnector.com</a>                                                                                                             |                                         |
| DO NOT SCALE DRAWING<br>DRAWING IS SUBJECT TO<br>CHANGE WITHOUT NOTICE                                      |  | TITLE:<br>EIGHT CONTACT, EIGHT POSITION; VERTICAL MOUNT SHIELDED JACK<br>NON-FLANGE                                                                                                                                                                                                                                       |                                         |
| DIMENSIONS: INCHES [METRIC]<br>UNLESS OTHERWISE SPECIFIED<br>TOLERANCES ARE ±.005 [0.13]<br>ANGLES ARE ± 1° |  | THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON<br>ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF<br>BEL STEWART CONNECTOR AND SHALL NOT BE REPRODUCED,<br>COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN<br>CONSENT OF BEL STEWART CONNECTOR. THE SUBJECT<br>MATTER MAY BE PATENTED OR A PATENT MAY BE PENDING. |                                         |
| SHEET NO. 1 OF 1                                                                                            |  | DRN BY: TRM<br>APPD BY: RGC<br>DWG NO. CT710020                                                                                                                                                                                                                                                                           | DATE 1-27-03<br>DATE 1-28-03<br>REV. A7 |

