

Shop By Category

+ Adapters

+ Amphenol Connectors

+ Audio Video Monitor Cables

+ CAT-5e • CAT-6 • Telco Cables

+ Coaxial Cables

+ CX4 Cables • InfiniBand Cables

+ DisplayPort Cables & Adapters

+ D-Sub Cables • D-Sub Adapters

+ Fiber Optic Patch Cables

+ Fibre Channel & DIN Cables

+ GPIB Cables (IEEE-488 Cables)

+ HDMI Cables (High Speed HDMI)

+ QSFP Cables • QSFP+ Cables

+ QSFP+ Modules & Loopbacks

+ QSFP-DD Cables • OSFP Cables

+ SAS Cables • SATA Cables

+ SCSI Cables • VHDCI Cables

+ SFP+ Cables • SFP+ Modules

+ SFP28 Cables • QSFP28 Cables

+ USB Cables

Shop By Application

+ Get 25 Percent OFF High Speed

+ 25/100-Gigabit Ethernet Tech

+ Custom Cables & Cable Kits

+ Data Center Cable Solutions

+ Home Theater AV Cable Center

More ways to Shop

+ Hot Items

+ New Items

+ Overstock

D-Sub Cables • D-Sub Adapters » D-Subminiature (D-Sub) Cables » 37-Pin D-Sub Cable (DB37) » CS-DSDMDB37MM

37-Pin (DB37) Deluxe D-Sub Cable - Copper Shielded - Male / Male

★★★★★ 2 Reviews



[Click for larger image](#)

37-pin (DB37) Copper Shielded High Density Male/Male D-Sub Cables by Amphenol provide exceptional performance in commercial, industrial or enterprise applications where longevity and repeated disconnects are required. Our fully assembled Deluxe HD D-Sub Cable integrates copper tape + aluminum mylar shielded 26 AWG data-grade wire with pre-terminated DB37 male d-sub connectors. Perfect for RS232 serial data, prototype, control and low-voltage applications using the 37-pin DB37 interface.

Product Features:

- Now Get 20% OFF This Cable at Checkout with Coupon Code: CABLE20
- 37-Pin (DB37) Deluxe Fully Populated D-Sub Cable Assembly by Amphenol
- Connectors: DB37 male to DB37 male D-Sub connectors pre-installed
- Cable: 26 AWG UL listed with copper tape + aluminum mylar shields
- Straight-through wiring (i.e. pin 1 to pin 1) design per industry standards
- Perfect for low-voltage signals & DCE/DTE RS232 serial communications
- 100% EMI/RFI shielded design combines aluminum mylar and copper tape
- Fully populated with Gold-plated contacts for superior signal continuity
- Rugged UL94V-0 flame-resistant PVC jacket and overmold for strain relief
- 300V voltage handling capacity at temperatures up to 80 degrees Celsius
- Available in multiple cable lengths to meet your specific requirements
- Cables can be easily cut in half and custom terminated for prototyping
- RoHS compliant

Item#	Color	Length	Qty 1-50	Qty >50	Availability	Order Qty
CS-DSDMDB37MM-002.5	Gray	2.5ft	\$	\$	In Stock	
CS-DSDMDB37MM-005	Gray	5ft	\$	\$	In Stock	
CS-DSDMDB37MM-010	Gray	10ft	\$	\$	In Stock	
CS-DSDMDB37MM-015	Gray	15ft	\$	\$	In Stock	
CS-DSDMDB37MM-025	Gray	25ft	\$	\$	In Stock	
CS-DSDMDB37MM-050	Gray	50ft	\$	\$	In Stock	

Add all entered quantities to cart - >

Similar Products

[37-Pin \(DB37\) Deluxe D-Sub Cable - Copper Shielded - Male / Female](#)



[37-Pin \(DB37\) Premium D-Sub Cable - Double Shielded + EMI Cage - Male / Female](#)



[37-Pin \(DB37\) Standard Shielded D-Sub Cable - Male / Female](#)



[37-Pin \(DB37\) Standard Shielded D-Sub Cable - Male / Male](#)



2019 Amphenol Corporation. All rights reserved.

Comments? | Privacy Statement | Business & Return Policies | Site Map

Sign up for our E-mail Newsletter

GO

Privacy by SafeSubscribeSM

Downloaded from [Arrow.com](#)