



Part Number : 191930303

Series Number : 19193

Product Category : Ring and Spade Terminals

Product Description : VersaKrimp Ring
Tongue Terminal for 2 AWG Wire, Closed-
Braze Barrel, Stud Size 10 (M5), Carton

Status : Active

Engineering Number : G-375-10

Documents & Resources

Drawings

Drawing 191930303_sd.pdf

3D Models and Design Files

3D Model 191930303_stp.zip

Specifications

Product Specification PS-19902-011-001.pdf

Product Specification PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 2 AWG Wire, Closed-Brazed Barrel, Stud Size 10 (M5), Carton
Keyword	Ring Terminal, Ring Terminals
Product Family	VersaKrimp Terminals and Splices
Product Name	VersaKrimp
Type	Ring
UPC	800755051490

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	13.553/g
Packaging Type	Carton
Stud Size	10 (M5)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	13.35mm max.
Wire Size (AWG)	2
Wire Size mm ²	35.00

Application Tooling

Global

Description	Part Number
Manual Putt Pump Hydraulic System, Die set required	<u>192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192900010</u>
Hydraulic Dieless Crimping Tool	<u>638161700</u>
Square "DIN" style dies for 2 AWG	<u>640037970</u>

This document was generated on May 07, 2024