

Power Extension Cord, NEMA 5-15P to NEMA 5-15R - 10A, 120V, 18 AWG, 15 ft. (4.57 m), Black

MODEL NUMBER: P022-015



15-foot extension cord connects two devices with 5-15P/5-15R power connectors or extends your existing power connection.

Features

15-ft. (4.57 m) Extension Cord Connects Computers, Printers, Servers and Other Equipment This power extension cable is designed for small data center or office workstation applications that do not require a heavy-gauge connection. With a NEMA 5-15P plug on one end and a NEMA 5-15R receptacle on the other, this cord can be used to power a computer, printer or monitor; attach a rack server to a UPS system or PDU; or extend an existing connection up to 15-ft. (4.57 m). The 15-ft. (4.57 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Specifications

OVERVIEW	
UPC Code	037332164841
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
PHYSICAL	
Cable Jacket Color	Black
Cable Jacket Material	PVC
Plug Color	Black

Highlights

- Recommended for powering computers, monitors and other essential peripherals
- Adds 15-ft. (4.57 m) to your existing connection to provide more flexibility in placing devices
- Ideal replacement for worn-out or missing 15-ft. (4.57 m) extension cord

Applications

- Connect devices like computers, servers and monitors to a PDU up to 15-ft. (4.57 m) away in your data center
- Extend an existing power connection up to 15-ft. (4.57 m) to more easily place a device or reach a power source away from your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P022-015 Power Extension Cord, NEMA 5-15P to NEMA 5-15R, 15-ft. (4.57 m), Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Jacket Rating	SJT
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	15
Cable Length (m)	4.57
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 0.25
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.10
Shipping Weight (kg)	0.41
Shipping Weight (lbs.)	0.90
ENVIRONMENTAL	
Operating Temperature Range	-4 TO 140 F (- 20° TO 60°C)
Storage Temperature Range	-4 TO 140 F (- 20° TO 60°C)
Operating Humidity Range	20-80% RH
Storage Humidity Range	20-80% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	NEMA 5-15R
SPECIAL FEATURES	
High Voltage	No
Locking Plug	No
Angled Plug	No
STANDARDS & COMPLIANCE	
Certifications	UL/Cul
Approvals	UL /CSA
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>