

Catalog

Home > Catalog



Home > 3108-B-1032-B

Swage Standoffs

Model: 3108-B-1032-B

Select Finish

Select Finish

Product Details

These standoffs are made of Brass. They are Round shaped with diameter as 3/8. The thread for this part is 10-32 and length is 3/16".

SWAGE TOOLING

±.003	S	P
.075	A	1/32
.105	B	1/16
.135	C	3/32
.165	D	1/8
.230	E	3/16
.290	F	1/4

PDF Catalog

[RAF_catalog_0099.pdf](#)

Thread	10-32
O.D.	3/8"
Shape	Round
Length (L)	3/16"
Material	Brass
RoHS	Yes
Shank Length	0.105"
Board Thickness	1/16"
Shank Diameter	0.234"
Thread Clearance	0.200"
Finish	-0 No Plate



In 2008, RAF joined with MW Industries Inc., www.mw-ind.com, to become the nation's leading supplier of electronic hardware components to a variety of industries, including computers, telecommunications, medical, entertainment and military/aerospace.

Technical Information


[Electronic Hardware Components](#)
[Engineering Data](#)
[Capabilities Brochure](#)
[Services](#)
[Distributors](#)

Company

[RAF Quality Management](#)
[Industry Links](#)
[What's New](#)
[News](#)
[About](#)
[Contact](#)
[Careers](#)

Contact Us

Find Us


 95 Silvermine Rd.
Seymour CT 06483

 Downloaded from [Arrow.com](#).