



- 1

MATERIAL: HOUSING- PBT, NATURAL  
POST- BRASS, 1MICROMETER MIN TIN OVER  
0.8 MICROMETER MIN NICKEL.
- 2

RECOMMENDED MATING PART: \*-1123722-\*
- 3

O : WITH PIN,  
X : WITHOUT PIN.
- 4

PRELIMINARY PART - NOT RELEASED FOR PRODUCTION

0	0	0	0	0	0	GREEN	6	6-1744106-7
0	0	X	0	X	0	BLACK	6	5-1744106-2
0	0	0	0	0	0	RED	6	4-1744106-7
0	X	0	0	0	0	RED	6	4-1744106-4
0	0	X	0	X	0	RED	6	4-1744106-2
0	0	0	0	0	0	BLUE	6	3-1744106-7
0	0	X	0	X	0	BLUE	6	3-1744106-2
0	0	0	0	0	0	YELLOW	6	2-1744106-7
0	0	X	0	X	0	YELLOW	6	2-1744106-2
0	0	X	0	X	0	NATURAL	6	1-1744106-2
X	0	X	0	X	0	NATURAL	6	1-1744106-1
0	0	0	0	X	0	BLACK	6	5-1744106-8
0	0	0	0	0	0	BLACK	6	5-1744106-7
0	0	0	0	0	0	NATURAL	6	1-1744106-7
0	X	0	X	0	0	NATURAL	6	1744106-6
0	0	X	0	0	0	NATURAL	6	1744106-5
0	X	0	0	0	0	NATURAL	6	1744106-4
0	X	0	0	X	0	NATURAL	6	1744106-3
0	0	0	X	0	0	NATURAL	6	1744106-2
0	0	0	0	X	0	NATURAL	6	1744106-1
1	2	3	4	5	6	COLOR	NO. OF POSITIONS	ASSEMBLY PART NO.

OBSOLETE

3

PIN POSITION

COLOR

NO. OF POSITIONS

ASSEMBLY PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

MATERIAL

TOLERANCES, UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	0.5
2 PLC	±	0.30
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH	±	-

1

DWN  
K. WHITAKER  
04JUN04

CHK  
D. BOSSI  
04JUN04

APVD  
D. BOSSI  
04JUN04

PRODUCT SPEC  
108-5609

APPLICATION SPEC  
-

WEIGHT  
0.000000

CUSTOMER DRAWING

TE Connectivity

NAME  
HEADER ASSEMBLY, SPECIAL,  
OMITTED POST, 6 POSITION,  
ECONOMY POWER (EP)

SIZE  
A2

CAGE CODE  
00779

DRAWING NO  
C=1744106

RESTRICTED TO  
-

SCALE  
N/A

SHEET  
1 OF 1

REV  
C4

1744106-1 SHOWN

METRIC