



Part Number : 1301020259  
Product Description : Safeway Phenolic Hand Lamp Only with 100W, Screw Release Guard with Reflector, with Switch and Side Outlet  
Series Number : 130102  
Status : Active  
Product Category : Lamps and Lights  
Engineering Number : 271US



## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
--------	--------

Category	Lamps and Lights
Series	130102
Description	Safeway Phenolic Hand Lamp Only with 100W, Screw Release Guard with Reflector, with Switch and Side Outlet
NEMA Configuration	N/A
Product Name	Safety Yellow
Type	Hand Lamps
UPC	78678860133

## Agency

CSA	LR85374
-----	---------

## Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	240V

## Physical

Bulb Type	Incandescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	101.60mm (4.000")
Duty	Commercial
Guard Included	Yes
Guard Type	Reflector, Screw Release
Height	381.00mm (15.000")
Lamp Type	A21
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Net Weight	681.748/g
Outlet	Side
Packaging Type	Carton

---

---

This document was generated on Apr 26, 2025