






Extended length is with 500g of force



P1	COLOR
1	WHITE
2	ORANGE
3	BLACK
4	RED
5	GREEN
6	YELLOW
7	BLUE
8	BROWN

Material:

- Plug Housing : Polycarbonate, clear
Plug Terminal: 0.36" [0.14MM] Thick Phosphor Bronze
- Connector: 50" of Selective Gold Contact Plating
 - Area, Gold flash over the remainder
 - Over 2.54μ[.000100] thick nickel underplate
- Conductor(X4C): 26AWG (0.12X12) Bare Copper
Insulation(X43): PP6331 ID 0.95-1.0
Jacket: PVC NOUL 80P
Package: Individual PE Bag



SEC: A-A

Extended Length ("L2")	Typical Retracted Length ("L1")
168.0 Inches - 193.2 Inches	75.0 Inches
4,267.2MM-4,907.28MM	1,905.0MM

Electrical:

- Voltage rating: 30V (DC)

[illegible]

Item No.	
----------	--

AT-C-26-8/8/S-14-OE

Title	NON-UL 26AWG (0.16/7)*8C, O.D.: 2.4*8.8MM, Single Plug, 50μ" of contact plating, Silver
--------------	--

Drawing No.

rev00

Replace

Sheet

