

DELPHI Connection Systems Catalog

Customer Service

Comparison List (0)

Sample Request

Find by Feature

Browse by Category

Browse by Application

Share

Search

Enter part number or keyword

Search Results (1)

Search Options

1 Result(s): [A//] - 13965727

☐ Compare

☐ F782100 - 4 Way Female AK Apex 1.2 SensoMate interface compatible pole A W/CPA

☐ Compare

«

<

1

>


»

4 Way Female AK Apex 1.2 SensoMate interface compatible pole A W/CPA

Part # F782100



Question about this product?

Attributes	Documents (1)	Related Products (7)
Part # :	F782100	
Description :	4 Way Female AK Apex 1.2 SensoMate interface compatible pole A W/CPA	
Product Type :	Connector	
Status :	 Active	
Family :	Apex	
Series :	1.2	
Cavities :	4	
Terminal(s) blade size [mm] :	1.2	
Sealable :	Sealed	
Gender :	Female	
Material :	PA	
Weight [g] :	0	
Connector Color :	Black	
Remarks :	Former FCI Product, Delphi PN: 13965727, APEX terminal technology and performance, SWS (Cable seal) terminal seal design, SensoMate 1.2 connectors mate to the popular European VDA/AK 1.2 device interface, Heavy Duty for Diesel engine vibration and temperature duty cycles, Compliant with USCAR design guidelines and performance standards, Terminal Position Assurance (TPA) device to detect partially installed terminals, mates Cam Sensor Device, mates CoilOnPlug Device, matesInjector	
Application :	Sensor - Engine	

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.