



Part Number : [135170001](#)

Product Description : Brick RFID Tag, 16.7m Read Range, 54.00 by 36.00mm Footprint, For Metal Surfaces, Screw or Rivet Attachment

Series Number : 13517

Status : Active

Product Category : Asset Tracking



Documents & Resources

Drawings

[135170001_sd.pdf](#)

Specifications

[135170001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[CE - Declaration of Conformity](#)

Part Details

General

Status	Active
Category	Asset Tracking
Series	13517
Description	Brick RFID Tag, 16.7m Read Range, 54.00 by 36.00mm Footprint, For Metal Surfaces, Screw or Rivet Attachment
Component Type	RFID Tag
Product Name	RFID Solutions
Type	For Metal Surfaces
UPC	196823154157

Electrical

Frequency	902-928 MHz
-----------	-------------

Physical

Length	54.00mm
Mounting Style	Adhesive, Screws
Packaging Type	Bag
Read Range	16.8m
Thickness	12.50mm
Width	36.00mm

This document was generated on Sep 18, 2025