



Color: ■ violet Similar to illustration

Technical data	
Marking method	Thermal transfer
Marking	11 ... 20
Marking (number)	10
Marking direction	Horizontal marking
Marking color	black
Marking type	Numbers
Marking layout	Consecutive numbers per strip
Delivery form	Marker card
Delivery form configuration	10 strips with 10 markers per card
Flammability class per UL94	V2

Physical data	
Height	152 mm / 5.984 inches
Width	56.8 mm / 2.236 inches
Depth	3.2 mm / 0.126 inches
Marker/strip width	5 mm
Marker width	5 mm

Mechanical data	
Smear resistance	EN 60998-1:2004

Material data	
Color	violet
UV resistance	EN 60068-2-5:2010 Procedure B
Halogen-free	Yes
Weight	6.7 g
Fire load	0.201 MJ



Commercial data	
Product Group	2 (Terminal Block Accessories)
PU (SPU)	5 (5) pcs
Packaging type	Foil
Country of origin	DE
GTIN	4066966572353
Customs tariff number	49119900000

Product Classification	
UNSPSC	55121718
eCl@ss 10.0	27-14-11-37
eCl@ss 9.0	27-14-11-37
ETIM 9.0	EC000761
ETIM 8.0	EC000761
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance
248-503/000-024

↓

Installation Notes

Marking



Marking via Mini-WSB Quick Marking System.