

SmartRack 6U Low-Profile Vertical-Mount Switch-Depth Wall-Mount Rack Enclosure Cabinet

MODEL NUMBER: **SRWF6U**



Wall-mount cabinet secures and organizes 6U of 19-inch rack equipment in network wiring closets and other locations with limited floor space. Houses equipment up to 20 inches deep, but extends less than 12 inches from wall.

Description

The SRWF6U SmartRack 6U Low-Profile Vertical-Mount Switch-Depth Wall-Mount Rack Enclosure Cabinet is designed to house EIA-standard 19-inch rack equipment in network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 150 lbs (68 kgs).

Because the low-profile cabinet mounts vertically, it extends less than 12 inches from the wall while housing equipment up to 20 inches deep, including network switches and patch panels. In addition to 6U of rack space in the primary mounting area, it also includes a slide-out 2U mounting bracket at the top of the enclosure for patch panels up to 2.5 inches deep.

The top panel and front door lock securely to help prevent damage, tampering or theft. The cabinet is vented, which allows air to flow freely and keep equipment cool. The reversible front door can open left or right. Convenient top and bottom ports allow easy cable routing.

The SRWF6U comes fully assembled and ready to mount to the wall. Equipment installation is easy with threaded mounting holes and hardware that support M6 or 12-24 mounting.

Features

Saves Valuable Workspace Perfect for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Houses EIA-standard 19 in. rack equipment in 6U of space. Low-profile vertical-mount cabinet extends less than 12 inches from the wall while housing equipment up to 20 inches deep, including network switches and patch panels. Also includes a slide-out 2U mounting bracket at the top of the enclosure for patch panels up to 2.5 inches deep. Maximum load capacity of 150 lbs (68 kgs).

Keeps Important Equipment Secure Top panel and reversible front door lock securely to help prevent damage, tampering or theft. Vented cabinet keeps equipment cool. Convenient ports with removable covers allow cable routing through top and bottom.

Easy Enclosure and Equipment Installation Ships fully assembled for quick installation. Wall-mounting holes spaced 16 in. apart for standard wall stud placement. Rails adjust easily—unscrew them, slide them to desired depth, and screw them back in. Threaded mounting holes support M6 or 12-24 mounting. Rack spaces marked for easy reference.

Highlights

- Maximum load capacity of 150 lbs (68 kgs)
- Locking steel cabinet vented to keep equipment cool
- Secures 6U of 19 in. rack equipment up to 20 in. deep
- Includes additional 2U of space for patch panels
- Ships fully assembled for quick installation

Package Includes

- SRWF6U SmartRack 6U Low-Profile Vertical-Mount Switch-Depth Wall-Mount Rack Enclosure Cabinet
- (12) M6 screws
- (12) M6 cup washers
- (12) 12-24 screws
- (2) Keys
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Meets Payment Card Industry Standards Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

Specifications

OVERVIEW	
UPC Code	037332190635
Device Compatibility	Patch Panel; Network Switch
Rack Type	Small Enclosure
PHYSICAL	
Color	Black
Rack Height	6U
Rack Depth	Shallow
Maximum Device Depth (cm)	50.80
Maximum Device Depth (in.)	20
Maximum Device Depth (mm)	508
Shipping Dimensions (hwd / in.)	34.25 x 31.10 x 16.93
Shipping Dimensions (hwd / cm)	87.00 x 78.99 x 43.00
Shipping Weight (lbs.)	70.50
Shipping Weight (kg)	31.98
Unit Dimensions (hwd / in.)	28.800 x 25.600 x 11.500
Unit Dimensions (hwd / cm)	73.15 x 65.02 x 29.21
Unit Weight (lbs.)	64
Unit Weight (kg)	29.03
Weight Capacity - Stationary (kg)	68
Weight Capacity - Stationary (lbs.)	150
Number of Vertical Mounting Rails	2
FEATURES & SPECIFICATIONS	
Built-in Cable Management	No
Extra Wide	No
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	

Product Warranty Period (Worldwide)	5-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.