molex



Part Number : 1300540023
Product Description : Ultra-Lock (M12) D-Coded to RJ-45 Adapter, Straight to Straight, 4-Pole Female to RJ45 Male, Unshielded PVC, 4.0m (13.12') Length
Series Number : 130054
Status : Obsolete
Product Category : Circular Industrial Connectors
Engineering Part Number : ERWPAB3002M040

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Obsolete
Category	Circular Industrial Connectors
Series	130054
Description	Ultra-Lock (M12) D-Coded to RJ-45 Adapter, Straight to Straight, 4-Pole Female to RJ45 Male, Unshielded PVC, 4.0m (13.12') Length
IP Rating	IP67
Product Name	RJ45,Ultra-Lock (M12)
Type	Double Ended
UPC	78678804288

Agency

UL	E200650

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	250V AC/DC

Physical

Coupling Type	Push to Lock
Gender	Female-Male
Keyway	D-Coded
Length	4.0m
Material - Component	Nickel-plated Brass
Mounting Thread Size	PG9
Net Weight	98.980/g
Orientation	Straight
Panel Mount	Back
Poles	4

Obsolete

Downloaded from Arrow.com.

Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	Unshielded PVC
Wire Size (AWG)	24

Obsolete

Downloaded from Arrow.com.