






THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Note:


- * \varnothing Important Dimension To Check.
- * Waterproof Rate: IP68(Mated)
- * Flame Class: UL94V-0 (UV Resistance)
- * Housing: Nylon+GF, Black.
- * Male Pin: Copper Alloy, Gold Plated.
- * Rated Current: 2~5Pin 5A(300V)
6~8Pin 2A(30V)
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		
TOLERANCE	±0.5mm	

TITLE X-Lok A-Size Molding M Conn M Pin			
SCALE 3:2	SIZE A4	SHEET 1 OF 2	
REV. A	WC-REV. .0	\varnothing : Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO AX-XXBMMM-QL8DXX	DRAWN BY Ouyang	DATE 2018-11-13
DWG NO AX-XXBMMM-QL8DXX	CHECKED BY Mafei	DATE 2018-11-13
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2018-11-13



2PIN	3PIN	4PIN	5PIN	6PIN	8PIN
CABLE: 20AWG*2C+AL/MY PIN OUT: 1.Black 2.Brown	CABLE: 20AWG*3C+AL/MY PIN OUT: 1.Black 4.Brown 3.Red	CABLE: 20AWG*4C+AL/MY PIN OUT: 1.Black 2.Brown 3.Red 4.Orange	CABLE: 20AWG*5C+AL/MY PIN OUT: 1.Black 2.Brown 3.Red 4.Orange 5.Yellow	CABLE: 24AWG*6C+AL/MY PIN OUT: 1.Black 2.Brown 3.Red 4.Orange 7.Yellow 6.Green	CABLE: 24AWG*8C+AL/MY PIN OUT: 1.Black 2.Brown 3.Red 4.Orange 5.Yellow 6.Green 7.Blue 8.Purple
AD-02BMMM-QL8DXX	AD-03BMMM-QL8DXX	AD-04BMMM-QL8DXX	AD-05BMMM-QL8DXX	AU-06BMMM-QL8DXX	AU-08BMMM-QL8DXX

UNIT:mm TOLERANCE ±0.5mm	TITLE X-Lok A-Size Molding M Conn M Pin		 安費諾亮泰企業股份有限公司	ITEM NO AX-XXBMMM-QL8DXX	DRAWN BY Ouyang	DATE 2018-11-13	
	SCALE 1:1	SIZE A4		SHEET 2 OF 2	DWG NO AX-XXBMMM-QL8DXX	CHECKED BY Mafei	DATE 2018-11-13
	REV. A	WC-REV. .0		Inspection item	CUSTOMER ALTW	APPROVED BY Jerry	DATE 2018-11-13